

scanDelay USB

The *scanDelay USB* is a device for introducing a well-defined linear translation and positioning of an optical element, e.g. in interferometers, pump-probe configurations, correlators, or fast scan modules.

The heart of the A·P·E optical delay line series *scanDelay USB* is a special linear translation stage that is supplied together with appropriate control and drive electronics. The linear drive has been designed especially for optical applications. It combines low moving mass with compactness, reaching a high speed, as well as high precision and resolution. Because of spring bearings the movement is frictionless.

Thus *scanDelay USB* is capable of generating fast wide scans as well as smallest delays without any stick-slip effects. The actual position is measured in real time by an analog photo-electric system with high resolution and wide dynamic range.

The linear drive allows precise predictions of the scanner movement and leads to an excellent scanto-scan reproducibility.

The control electronics contain the motor driver and a quartz stabilized signal synthesizer. It can be synchronized with an external clock for a precise, phase-locked scanner movement. A software user interface allows easy control and setup of the scanner. A set of LabView drivers allows an easy integration into existing measurement software. The *scanDelay USB* can be operated over a wide range of scanning frequencies with various scan modi, the motor driving force can be sinusoidal, triangular, sawtooth-like, or even of a user defined shape. The scanner movement will respond to this within the physical limitations imposed by a harmonic system.

- Control Software | LabView drivers
- User defined delay patterns
- Scan rate phase-locked to external source www.phototechnica.co.jp
- Linear and Sale Only 通生機能では、 measurem Hallyocomphototechnica.co.jp



Optical Delay Line

Specifications

Version	15	50	150
Max. scan range	15 ps (± 1.125 mm)	50 ps (± 3.75 mm)	150 ps (± 11.25 mm)
Scan modes			
Internal generator ¹⁾	0.1 20 Hz	0.1 20 Hz	0.1 10 Hz
Externally triggered ¹⁾	0.01 20 Hz	0.01 20 Hz	0.01 10 Hz
External trigger intput	TTL, 20 Hz < 50 kH	z (fast frequency divide	r for approx. 80 MHz input optional)
Trigger output (programmab	le position)	TTL	
Position output signal	± 10 V ²⁾ 15 ps	± 10 V ²⁾ 50 ps	± 10 V ²⁾ 150 ps
Linearity of position signal		< 0.5 %	
Computer interface		USB	
Optics (high precision retro reflector)			
Clear aperture	1 "	1/2 "	1/2 "
Coating	protected Ag (other coatings on request)		

Internal position sampling and indication of amplitude (maximum delay) in Control Software from 0.4 ... 20 Hz only.
 Below 0.4 Hz scan frequency, only partial (smaller than maximum delay) scan position is displayed.
 Full position information is available via analog position output signal.

Optical head

Compatibility of the Control Software with Windows 8 operating system is being tested. Windows is a registered trademark of Microsoft Corporation in the United States and other countries.




Powers I will be a second particle with the se

Control electronics

Dimensions (in mm)

Optical unit

Control electronics



Contact:

A-P-E Angewandte Physik & Elektronik GmbH
Plauener Str. 163-165 | Haus N | 13053 Berlin | Germany
T: +49 30 986 011-30 | E: sales@ape-berlin.de | www.ape-berlin.com
or
A-P-E America (for the Americas)

T: +1 (888) 690 3250 | E: sales@ape-america.com | www.ape-america.com

45401 Research Avenue | Suite 141 | Fremont, CA 94539 | USA

www.phototechnica.co.jp TECHNICA フォトテクニカ株式会社 〒336-0017 埼玉県さいたま市南区南浦和 1-2-17 TEL:048-871-0067 FAX:048-871-0068 e-mail:voc@phototechnica.co.jp

A·P·E follows a policy of continued product improvement. Therefore, specifications are subject to change without notice. @ A·P·E GmbH| January 2015

²⁾ x10, x100 switchable